

## Accessories Light Control Accessories

## **Light Control Accessories**

The Juno complete range of light control accessories permit the designer

| ustom tailor ef<br><b>Accessory</b> |   |  | 1 3/4"<br>DIA. | COMPATIBLE<br>WITH   | 2"<br>DIA.  | COMPATIBLE<br>WITH   |
|-------------------------------------|---|--|----------------|--|---|--|
| 0                                   | Required for listed fixtures.<br>Accepts one filter, lens, and<br>louver except where noted.  |  |                |  | T7400BL<br>T7400SA<br>Accepts up<br>to 2<br>accessories | T227, T401, T630   |
| UV Filters                          |   |  |                |  |   |  |
| Dichroic C                          | These museum quality lenses filter out ultraviolet radiation below 400 nanometers to protect fade sensitive art and objects.          |  | T5522          | T160, T161, T165,<br>T196, T216,<br>T290**, T291,<br>T338**, T340**,<br>T350, T406*, | T7422   | T640*, T811*,<br>T812*, T814,<br>T816*, T817*,<br>T819*, T841*,<br>T850*, T870*,<br>T880*, T870*,<br>TM141*, TM241*,<br>XT16 Halogen<br>Series, XT16 CMH |
|                                     | Color Correction Filters correct  | Halogen-to-Incandescent,                         |                | T430, T442, T443,<br>T447, T480, T621,   |   |  |
|                                     | the light, either to warm it up to approximate incandescent,  | 2700K  | T5518          | T696, T805, T807,  | T7418   | Series and<br>fixtures with  |
|                                     | or cool it down to approximate daylight.  | Halogen-to-Daylight,  4250K  HID-to-Incandescent | T5516          | T809, TP216,<br>TP443  | T7416   | T7400 Accessory<br>Holder  |
|                                     |   | for HID Lampholders                              |                |  | T7419   |  |
| Color Filters Colored Glass Filters |   | Colored Glass Filters                            |                | _  |   |  |
|                                     | Color Filters change white light into colored light and are available in colored glass and more efficient/saturated dichroic filters. | Medium Pink                                      | T551           | 1  | T741  | -<br>-<br>-  |
|                                     |   | Warm Red   |                |  | T742  |  |
|                                     |   | Daylight Blue                                    | TEFO           |  | T743  |  |
|                                     |   | Medium Blue  Medium Amber                        | T553<br>T555   |  | T744<br>T745  |  |
|                                     |   | Medium Green                                     | 1555           | -  | T746  |  |
|                                     |   | Dichroic Glass Filters                           |                |  |   |  |
|                                     |   | Red  | T5501          |  | T7401   |  |
|                                     |   | Medium Green                                     | T5503          | -  | T7403   |  |
|                                     |   | Medium Blue                                      | T5504          |  | T7404   |  |
|                                     |   | Yellow   | T5505          |  | T7405   |  |
|                                     |   | Magenta  | T5506          | -  | T7406   |  |
| Light Control Lenses                |   | T5511  |                | T7411  |   |  |
|                                     | These alter the light distribution  | Uniformity Lens                                  | T5521          | T160, T165, T196,  | T7421   |  |
|                                     | of a given lamp, enlarging or elongating it, softening the beam   | Diffusion Lens                                   | T5520          | T216, T290**,  | T7420   |  |
|                                     | edge or removing striations.  | Prismatic Spread Lens                            | T557           | T291, T338**,<br>- T340**, T350,   | T7477   |  |
|                                     |   | Linear Spread Lens                               | T559           | T406, T430, T442,  | T7478   |  |
|                                     |   |  |                | T443, T447, T480,  |   |  |
|                                     |   |  |                | T621, T696, T805,<br>T807, T809,   |   |  |
| Louvers                             |   |  |                | TP216, TP443   |   |  |
|                                     | Hexcell and Cube Cell louvers   | Hexcell Louvers                                  | T5559BL        |  | T7459BL   |  |
| 19                                  | reduce perceived fixture  | Cube Cell Louvers                                |                |  |   |  |
|                                     | brightness.   |  |                |  |   |  |
|                                     |   |  |                |  |   |  |
|                                     |   |  |                |  |   |  |
|                                     |   |  |                |  |   |  |
|                                     |   |  |                |  |   |  |
|                                     |   |  |                |  |   |  |



<sup>\*</sup>Simultaneously accepts any combination of up to two filters, lenses or louver.

\*\*T338, T340 can accept 1 3/4\* filters, lenses and louver standard and can also accept 4 11/16\* filters, lenses and louver when combined with T570 Accessory Holder or T72 Barn Door accessory. T290 can accept 1 3/4\* filters, lenses and louver standard and can also accept 3 3/4\* filters, lenses and louver standard.