
Cubix®

The Cubix is a study of the visual relationship between two different geometric forms: the ring and the cube. In this design, the stem becomes a central element, forming a pleasing visual extension of the cube form. Concealed wiring and sleek trac adapter offer an ultra-clean appearance. Cubix for Trac-Master is designed for use with 50W PAR20, 75W PAR30, and 150W PAR38 line-voltage halogen lamps and 50W MR16 low-voltage halogen lamps. An optional, integral, bayonet-mount media cartridge is available for the PAR30 fixture that simultaneously accepts up to two light control accessories. A dual accessory media cartridge is standard on the MR16 fixture.



Catalog # T890WH T890BL T890SL **Finish**White
Black
Silver

Lamp 12V, 20-50W MR16




T537 or T538 Transformer required. Must order separately. See page 821 for detailed information.

7

Catalog # T892WH T892BL T892SL Finish
White
Black
Silver

Lamp 35-50W PAR20






Catalog # T893WH T893BL T893SL Finish
White
Black
Silver

35-75W PAR30

Lamp






Catalog # T898WH T898BL T898SL Finish
White
Black
Silver

45-150W PAR38

Lamp




Light Control Accessories


| For Fixtures: | T890 | T893 |
|-----------------------|----------|---------------------|
| Accessory Holder* | - | T893MC-WH, -BL, -SL |
| Color Filters/Lenses | T741-6 | T561-6* |
| Prismatic Spread Lens | T7477 | T5677* |
| Linear Spread Lens | T7478 | T5678* |
| Dichroic Lenses | T7401-18 | T5618* |
| Diffuse Spread Lens | T7420 | - |
| Uniformity Lens | T7421 | T5621* |
| UV Filter Lens | T7422 | T5622* |
| Hexcell Louver | T7459BL | - |
| Cube Cell Louver | - | T569BL* |

^{*}Filters, lenses and louver require dual accessory holder for installation.

20-75VA 12V Transformers

Both **T537** and **T538** are available in white, black or silver finishes. See page 821 for a full description, or page 819 for Monopoint Transformers.





JUNO LIGHTING GROUP

Low Voltage Cubix® & Glacis®



Cubix®

The Cubix is a study of the visual relationship between two different geometric forms: the ring and the cube. In this design, the stem becomes a central element, forming a pleasing visual extension of the cube form. Concealed wiring offers an ultra-clean appearance. Cubix for Trac-Master is designed to use 50W MR16 halogen lamps. A dual accessory media cartridge is standard on the MR16 fixture.

Finish

White

Black

Silver

| Dimensions | | |
|------------|--|--|
| 4 3/8" | | |
| 5 3/4" | | |

| # |
|---|
| |
| |
| |
| |

Lamp

12V, 20-50W MR16



T537 or T538 transformer required. Must order separately. See page 821 for detailed information.

Glacis®

The Glacis is inspired by the beauty of our natural world. The truncated conical element at the top cloaks the stem pivot when observed from conventional viewing angles. Concealed wiring completes the ultra-clean appearance. Glacis for Trac-Master low voltage is designed to use 50W MR16 halogen lamps. Media cartridge for two light control accessories is standard on the MR16 fixture.

| Dimensions | | |
|------------|--------|--|
| 4 11/16" | 3/8" → | |

| Catalog # |
|-----------|
| T880WH |
| T880BL |
| T880SL |
| |

Finish White Black Silver

Lamp

12V, 20-50W MR16



T537 or T538 transformer required. Must order separately. See page 821 for detailed information.

Light Control Accessories

| For Fixtures: | T880, T890 |
|-----------------------|------------|
| Color Filters/Lenses | T741-6 |
| Prismatic Spread Lens | T7477 |
| Linear Spread Lens | T7478 |
| Dichroic Lenses | T7401-18 |
| Diffuse Spread Lens | T7420 |
| Uniformity Lens | T7421 |
| UV Filter Lens | T7422 |
| Hexcell Louver | T7459BL |

20-75VA 12V Transformers

Both **T537** and **T538** are available in white, black or silver finishes. See page 821 for a full description, or page 819 for Monopoint Transformers.

